

# COLD WORK TOOL STEELS

#### **Available Product Variants**

Long Products*	Plates

\*) Presented data refer exclusivly to long products. Please observe the detailed explanations at the end of the data sheet (pdf).

## **Product Description**

BÖHLER K110 is a 12% ledeburitic chromium steel and corresponds to material number 1.2379 (X153CrMoV12, D2). This tool steel combines the advantages of conventional 12% ledeburitic chromium steels with those of advanced tool steels. In the group of 12% ledeburitic chromium steels, BÖHLER K110 offers the best combination of wear resistance, compressive strength and toughness, for which reason it is used in virtually all cold work applications. Its advantageous tempering behavior with a pronounced secondary hardness maximum also enables the use of advanced coatings. This also makes BÖHLER K110 suitable for complex tools requiring a high degree of dimensional stability and shape stability.

#### **Process Melting**

Airmelted

#### **Properties**

- > Wear Resistance : good
- > Dimensional stability : good

#### **Applications**

- > Machine knife (for producers)
- > Coining
- > Standard Parts (Molds, Plates, Pins, Punches)
- > Components for underground construction (drilling, shafts, etc.)
- > General Components for Mechanical Engineering
- > Rolling
- Fine Blanking, Stamping, > Blanking
- > Screws and Barrels
- > Rolls
- > Thread rolling

- > Cold Forming
- > Powder Pressing
- > Components for the recycling industry
- > Wear parts

## **Technical data**

Material designation	
1.2379	SEL
X153CrMoV12	EN
~T30402	UNS
D2	AISI

Standards		
	4957	en iso





## Chemical composition (wt. %)

С	Si	Mn	Cr	Мо	V
1.55	0.30	0.30	11.30	0.75	0.75

## **Material characteristics**

	Compressive strength	strength stability during heat treatment abrasive		Wear resistance adhesive		
BÖHLER K110	**	***	*	***	**	
BÖHLER K100	**	**	*	***	**	
BÖHLER K105	**	**	*	**	**	
BÖHLER K107	**	**	*	***	**	
<b>BÖHLER K190</b> MICROCLEAN	****	****	****	****	****	
BÖHLER K294 MICROCLEAN	****	****			****	
BÖHLER K340 ECOSTAR	***	***	**	**	**	
BÖHLER K340 ISODUR	***	****	***	***	****	
BÖHLER K346	***	***	***	****	**	
BÖHLER K353	**	***	**	** **		
<b>BÖHLER K360</b> ISODUR	***	****	***	*** ***		
<b>BÖHLER K390</b> MICROCLEAN	****	****	**** ****		****	
<b>BÖHLER K490</b> MICROCLEAN	****	****	**** ****		****	
<b>BÖHLER K497</b> MICROCLEAN	****	****	*** ****		****	
<b>BÖHLER K888</b> MATRIX	****	****	**** **		**	
BÖHLER K890 MICROCLEAN	****	****	****	***	***	

## **Delivery condition**

#### Annealed

	Hardness (HB)	max. 250
--	---------------	----------






#### Heat treatment

Temperature	800 to 850 °C	Slow controlled cooling in furnace at a rate of 10 to 20 °C/hr (18 to 36 °F/hr) down to approximately 600 °C (1112 °F)    Further cooling in air.
<b>c</b> , <b>r</b> ,		
Stress relieving		After through heating, hold in neutral atmosphere for 1-2 hours.    Slow cooling in furnace

#### Hardening and Tempering

TemperatureQuenching: Oil, salt bath (220 to 250 °C or 500 to 550 °C   428 to 482 °F or 932 to 1022 °F), gas, compressed or still air. Tools of intricate shape or with sharp edges should preferably be hardened in air.    Holding time after temperature equalization: 15 to 30 minutes.    After hardening, tempering to the desired working hardness according to the tempering chart.	
--	--

### **Tempering chart**



Specimen size: square 20 mm (0,787 inch)

Slow heating to tempering temperature immediately after hardening.

Time in furnace 1 hour for each 20 mm (0,787 inch) of workpiece thickness but at least 2 hours.

Please refer to the tempering chart for guide values for the achievable hardness after tempering.

It is recommended to temper at least three times above the secondary hardness maximum.


Cooling in air to room temperature after each tempering step is recommended.

Tempering for stress relieving 30 to 50  $^{\circ}$ C (86 to 122  $^{\circ}$ F) below the highest tempering temperature.


Recommended tempering temperature range is indicated by the blue area in the chart.



## Continuous cooling CCT curves



## Quantitative phase diagram



HV10... Vickers Hardness Lk... Ledeburite carbide RA... Residual austenite M... Martensite B... Bainite P... Perlite

Austenitising temperature: 1080 °C (1976 °F) Holding time: 30 minutes

0.40...59.8 cooling parameter  $\lambda_{r}$  i.e. duration of cooling from 800 to 500 °C (1472 to 932 °F) in s x  $10^{-2}$ 

1...2 K/min... cooling rate in the range of 800 to 500  $^\circ\mathrm{C}$  (1472 to 932  $^\circ\mathrm{F})$ 

M... Martensite Ms... Martensite starting temperature

O Vickers hardness

A... Austenite

K... Carbide P... Perlite

B...Bainite

2...100 phase percentages

--- Oil cooling --- Air cooling


1... Edge or face 2... Core



voestalpine BÖHLER Edelstahl GmbH & Co KG https://www.voestalpine.com/bohler-edelstahl/de/




## Isothermal TTT curves



Austenitising temperature: 1020 °C / 1868 °F Holding time: 30 minutes

A... Austenite K... Carbide P... Perlite B... Bainite M... Martensite Ms... Martensite starting temperature

#### Influence of work diameter on core hardness and hardness penetration




Quenched from: 1030 °C / 1886 °F

Quenchant: Oil





## Heat treatment sequence



## **Physical Properties**

Temperature (°C)	20
Density (kg/dm <sup>3</sup> )	7.67
Thermal conductivity (W/(m.K))	23.9
Specific heat (kJ/kg K)	0.47
Spec. electrical resistance (Ohm.mm²/m)	0.65
Modulus of elasticity (10 <sup>3</sup> N/mm <sup>2</sup> )	200





#### Thermal Expansions between 20°C | 68°F and ...

Temperature (°C)	100	200	300	400	500	600	700
Thermal expansion (10 <sup>-6</sup> m/(m.K))	11	11.4	11.9	12.2	12.7	12.8	12.1

Long Products: For additional specifications and technical requirements, please contact our regional voestalpine BÖHLER sales companies.

Sheet & Plates: Product Variant may differ in terms of melting process, technical data, delivery, and surface condition as well as available product dimensions. Please contact voestalpine BÖHLER Bleche GmbH & Co KG.

The data contained in this brochure is merely for general information and therefore shall not be binding on the company. We may be bound only through a contract explicitly stipulating such data as binding. Measurement data are laboratory values and can deviate from practical analyses. The manufacture of our products does not involve the use of substances detrimental to health or to the ozone layer.

voestalpine BÖHLER Edelstahl GmbH & Co KG Mariazeller Straße 25 8605 Kapfenberg, AT T. +43/50304/20-0 E. info@bohler-edelstahl.at https://www.voestalpine.com/bohler-edelstahl/de/

